


USA 10-KSS - Rail adapter

3034379

<https://www.phoenixcontact.com/us/products/3034379>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Rail adapter, for accommodating the KSS 8 and KSS 10 short-circuit plug, depth: 19 mm, width: 10 mm, height: 42.6 mm, color: gray



Your advantages

- The universal adapters are used to secure and hold electrical or electronic switching devices
- They allow fully insulated mounting of components or DIN rails

Commercial data

Item number	3034379
Packing unit	50 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	BE61ZX
GTIN	4055626276809
Weight per piece (including packing)	2 g
Weight per piece (excluding packing)	2 g
Country of origin	DE

USA 10-KSS - Rail adapter

3034379

<https://www.phoenixcontact.com/us/products/3034379>



Technical data

Product properties

Product type	Mounting material
--------------	-------------------

Dimensions

Width	10 mm
Height	42.6 mm
Depth	19 mm

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V2
Coating	uncoated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

USA 10-KSS - Rail adapter

3034379

<https://www.phoenixcontact.com/us/products/3034379>



Classifications

ECLASS

ECLASS-13.0	27370419
ECLASS-15.0	27370419

ETIM

ETIM 10.0	EC001024
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

USA 10-KSS - Rail adapter

3034379

<https://www.phoenixcontact.com/us/products/3034379>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.017 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com