DIO-FIX SKN 5-4 - Plug bracket

3036801

https://www.phoenixcontact.com/us/products/3036801

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug bracket, for SKN 5 diodes, pitch: 5.2 mm, depth: 35.2 mm, width: 19 mm, height: 4 mm, mounting type: Plug-in mounting

Commercial data

Item number	3036801
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z3X
GTIN	4055626299662
Weight per piece (including packing)	3.7 g
Weight per piece (excluding packing)	3.7 g
Customs tariff number	85389099
Country of origin	CN

Technical data

Product properties

Product type	Mounting material
Pitch	5.2 mm

Dimensions

Width	19 mm
Height	4 mm
Depth	35.2 mm
Hole diameter	4.2 mm
Pitch	5.2 mm
Max. material thickness	1.6 mm

Material specifications

Material	Copper, tin-plated

Classifications

ECLASS

ECLASS-15.0	27141190
ECLASS-13.0	27141190

ETIM

ETIM 10.0	EC002848

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com