


D-STTCO 2,5 GY - Lateral element

3038406

<https://www.phoenixcontact.com/us/products/3038406>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Side cover, for closing the housing for IP20 protection

Commercial data

Item number	3038406
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AC11
Product key	ACHCDA
GTIN	4017918952594
Weight per piece (including packing)	7.31 g
Weight per piece (excluding packing)	5.91 g
Customs tariff number	85389099
Country of origin	DE

D-STTCO 2,5 GY - Lateral element



3038406

<https://www.phoenixcontact.com/us/products/3038406>

Technical data

Product properties

Product type	Panel mounting base side part
Housing series	STTCO
Number of positions	4
	5

Dimensions

Width	2.5 mm
Height	91 mm
Depth	62.3 mm

Material specifications

Color (Housing)	anthracite gray (RAL 7016)
Material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

D-STTCO 2,5 GY - Lateral element



3038406

<https://www.phoenixcontact.com/us/products/3038406>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3038406>



UL Recognized

Approval ID: E240868

D-STTCO 2,5 GY - Lateral element



3038406

<https://www.phoenixcontact.com/us/products/3038406>

Classifications

ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

D-STTCO 2,5 GY - Lateral element



3038406

<https://www.phoenixcontact.com/us/products/3038406>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com