

DP-PT 2,5-HEXA/3P - Spacer plate



3040060

<https://www.phoenixcontact.com/us/products/3040060>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Spacer plate, depth: 35.3 mm, width: 5.2 mm, height: 111 mm, color: orange, mounting type: NS 35/7,5



Commercial data

Item number	3040060
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	BE2Z1X
GTIN	4046356925501
Weight per piece (including packing)	8.256 g
Weight per piece (excluding packing)	7.965 g
Country of origin	PL

DP-PT 2,5-HEXA/3P - Spacer plate



3040060

<https://www.phoenixcontact.com/us/products/3040060>

Technical data

Product properties

Product type	Distance terminal
--------------	-------------------

Dimensions

Width	5.2 mm
Height	111 mm
Depth	35.3 mm
Depth on NS 35/7,5	35.3 mm

Material specifications

Color	orange (RAL 2003)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 35/7,5
	NS 35/15

DP-PT 2,5-HEXA/3P - Spacer plate



3040060

<https://www.phoenixcontact.com/us/products/3040060>

Classifications

ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

ETIM

ETIM 10.0	EC000886
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

DP-PT 2,5-HEXA/3P - Spacer plate



3040060

<https://www.phoenixcontact.com/us/products/3040060>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.071 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com