

FBI 2-15 IB - Fixed bridge

3057319

<https://www.phoenixcontact.com/us/products/3057319>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fixed bridge, with Allen screws and SW 4 (wrench size), number of positions: 2, color: silver-colored

Commercial data

Item number	3057319
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	BE1Z2X
GTIN	4046356501347
Weight per piece (including packing)	19.864 g
Weight per piece (excluding packing)	19.789 g
Country of origin	CN

FBI 2-15 IB - Fixed bridge

3057319

<https://www.phoenixcontact.com/us/products/3057319>



Technical data

Product properties

Product type	Screw bridge
Number of positions	2

Material specifications

Color	silver-colored
Material	Cu

Mounting

Mounting type	Screw mounting
---------------	----------------

FBI 2-15 IB - Fixed bridge

3057319

<https://www.phoenixcontact.com/us/products/3057319>



Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FBI 2-15 IB - Fixed bridge



3057319

<https://www.phoenixcontact.com/us/products/3057319>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com