

AP RSC-T - Cover profile

3059139

<https://www.phoenixcontact.com/us/products/3059139>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover profile, for covering terminal strips, directly snapped onto RBO... and RSC... test disconnect terminal blocks. Length supplied: 1 m

Commercial data

Item number	3059139
Packing unit	10 m
Minimum order quantity	10 m
Sales key	BE06
Product key	BE61ZX
GTIN	4046356520799
Weight per piece (including packing)	241 g
Weight per piece (excluding packing)	241 g
Customs tariff number	39162000
Country of origin	DE

AP RSC-T - Cover profile

3059139

<https://www.phoenixcontact.com/us/products/3059139>



Technical data

Product properties

Product type	Cover profile
--------------	---------------

Dimensions

Width	78.4 mm
Height	1000 mm
Depth	18.6 mm
Length	1000 mm

Material specifications

Color	transparent
Material	PVC
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

AP RSC-T - Cover profile

3059139

<https://www.phoenixcontact.com/us/products/3059139>



Classifications

ECLASS

ECLASS-15.0	27141190
ECLASS-13.0	27141190

ETIM

ETIM 10.0	EC002848
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

AP RSC-T - Cover profile



3059139

<https://www.phoenixcontact.com/us/products/3059139>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com