

FUSE 10,3X38 15A PV A - Fuse



3062784

<https://www.phoenixcontact.com/us/products/3062784>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse, for the photovoltaics industry according to UL 2579, nom. voltage: 1000 V, nominal current: 15 A, height: 38 mm, diameter: 10.3 mm, color: white

Your advantages

- Use in PV lines with a nominal voltage of up to 1000 V DC
- Designed in accordance with the photovoltaic standard UL 2579
- 10 x 38 midjet fuses for reliable protection of PV modules and their control system

Commercial data

Item number	3062784
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z4X
GTIN	4046356768221
Weight per piece (including packing)	9.13 g
Weight per piece (excluding packing)	8.82 g
Customs tariff number	85361050
Country of origin	SI

FUSE 10,3X38 15A PV A - Fuse



3062784

<https://www.phoenixcontact.com/us/products/3062784>

Technical data

Product properties

Product type	Fuse
--------------	------

Electrical properties

Fuse	15 A Midget / 10.3 x 38
------	-------------------------

Fuse

Power dissipation	2.2 W
Power dissipation $0.7 \times I_N$	1 W
Melting integral I^2t	49 A ² s
Disconnect integral I^2t	145 A ² s

Connection data

Connection in acc. with standard	IEC 60269-6
Nominal current	15 A
Nominal voltage	1000 V DC

Dimensions

Height	38 mm
Diameter	10.3 mm

Material specifications

Color	white (RAL 9010)
-------	------------------

Standards and regulations

Connection in acc. with standard	IEC 60269-6
----------------------------------	-------------

FUSE 10,3X38 15A PV A - Fuse



3062784

<https://www.phoenixcontact.com/us/products/3062784>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3062784>



EAC

Approval ID: RU C-DE.BL08.B.00724



UL Listed

Approval ID: E360477

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	1000 V	-	-	-

FUSE 10,3X38 15A PV A - Fuse



3062784

<https://www.phoenixcontact.com/us/products/3062784>

Classifications

ECLASS

ECLASS-13.0	27142002
ECLASS-15.0	27142002

ETIM

ETIM 10.0	EC002704
-----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

FUSE 10,3X38 15A PV A - Fuse



3062784

<https://www.phoenixcontact.com/us/products/3062784>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com