

KDT 29-30 - Cable sleeve

3063390

<https://www.phoenixcontact.com/us/products/3063390>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Small, slotted cable sleeves suitable for conductors with a diameter of 29 ... 30 mm.



The figure shows the KDT 20-21 product

Product description

Slotted sleeves for accommodating preassembled cables and lines with a diameter of 29 mm ... 30 mm, can be used in CES sealing frames: KEL 16/4, KEL 16/8, KEL 24/4, KEL 24/5, KEL 24/7, KEL 24/10.

Commercial data

Item number	3063390
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	AF7CCX
GTIN	4046356301176
Weight per piece (including packing)	23.97 g
Weight per piece (excluding packing)	23.97 g
Customs tariff number	40169300
Country of origin	DE

KDT 29-30 - Cable sleeve

3063390

<https://www.phoenixcontact.com/us/products/3063390>



Technical data

Product properties

Product type	Cable sleeve
No. of conductors	1

Material specifications

Material	Elastomer
Flammability rating according to UL 94	V0

Cable/line

External cable diameter	29 mm ... 30 mm
-------------------------	-----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 80 °C

KDT 29-30 - Cable sleeve

3063390

<https://www.phoenixcontact.com/us/products/3063390>



Classifications

ECLASS

ECLASS-13.0	27144425
ECLASS-15.0	27144425

KDT 29-30 - Cable sleeve

3063390

<https://www.phoenixcontact.com/us/products/3063390>



Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com