

KDT 4/4 - Cable sleeve

3063455

<https://www.phoenixcontact.com/us/products/3063455>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Small, slotted cable sleeves suitable for four conductors with a diameter of 4 x 4 mm.

Product description

Slotted sleeves for accommodation of four conductors with a 4 x 4 mm diameter, can be used in KEL sealing frames: KEL 16/4, KEL 16/8, KEL 24/4, KEL 24/5, KEL 24/7, KEL 24/10. The sleeves also serve as strain relief devices as per DIN EN 50262 when installed.

Commercial data

Item number	3063455
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	AF7CCX
GTIN	4046356301305
Weight per piece (including packing)	8.15 g
Weight per piece (excluding packing)	8.15 g
Customs tariff number	40169300
Country of origin	DE

KDT 4/4 - Cable sleeve

3063455

<https://www.phoenixcontact.com/us/products/3063455>



Technical data

Product properties

Product type	Cable sleeve
No. of conductors	4

Material specifications

Material	Elastomer
Flammability rating according to UL 94	V0

Cable/line

External cable diameter	4 mm
-------------------------	------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 80 °C

KDT 4/4 - Cable sleeve



3063455

<https://www.phoenixcontact.com/us/products/3063455>

Classifications

ECLASS

ECLASS-13.0	27144425
ECLASS-15.0	27144425

KDT 4/4 - Cable sleeve



3063455

<https://www.phoenixcontact.com/us/products/3063455>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com