

# TMB-QT 2,5/20-B 194 - Assembled cable connectors



3207753

<https://www.phoenixcontact.com/us/products/3207753>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled cable connectors

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3207753       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF19          |
| Product key                          | AF8EAA        |
| GTIN                                 | 4046356058001 |
| Weight per piece (including packing) | 262.4 g       |
| Weight per piece (excluding packing) | 258.3 g       |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

# TMB-QT 2,5/20-B 194 - Assembled cable connectors





3207753

<https://www.phoenixcontact.com/us/products/3207753>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3207753>

|  <b>CSA</b><br>Approval ID: 13631 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| C  | 600 V                 | 20 A                  | - 14              | -                           |

|  <b>UL Recognized</b><br>Approval ID: E118976 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  | 600 V                 | 20 A                  | - 14              | -                           |

3207753

<https://www.phoenixcontact.com/us/products/3207753>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060390 |
| ECLASS-15.0 | 27061801 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC003249 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

3207753

<https://www.phoenixcontact.com/us/products/3207753>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 1.721 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)