

EC 2,5 P TR - Europe connectors



3240167

<https://www.phoenixcontact.com/us/products/3240167>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Polyamide Europe terminal strip, transparent, with wire protection, for connecting solid conductors and stranded conductors with and without ferrules with a cross section of 0.5 to 2.5 mm²

Commercial data

Item number	3240167
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE73
Product key	BE7322
GTIN	4046356457903
Weight per piece (including packing)	20.07 g
Weight per piece (excluding packing)	20.07 g
Customs tariff number	85369010
Country of origin	AT

EC 2,5 P TR - Europe connectors



3240167

<https://www.phoenixcontact.com/us/products/3240167>

Technical data

Product properties

Product type	Europe connector
Number of positions	12
Pitch	8 mm
Number of connections	24
Number of rows	1

Electrical properties

Maximum power dissipation for nominal condition	0.77 W
---	--------

Connection data

Nominal cross section	2.5 mm ²
Connection method	Screw connection
Screw thread	M2,6
Tightening torque	0.4 ... 0.5 Nm
Stripping length	5 mm
Conductor cross-section rigid	0.5 mm ² ... 2.5 mm ²
Cross section AWG	20 ... 14 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 2.5 mm ²
Conductor cross-section, flexible [AWG]	20 ... 14 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 1.5 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 1 mm ²
2 conductors with same cross section, rigid	0.5 mm ² ... 0.75 mm ²
2 conductors with same cross section, flexible	0.5 mm ² ... 0.75 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ²
Nominal cross section	2.5 mm ²
Nominal current	24 A (with a 2.5 mm ² conductor cross-section)
Maximum load current	24 A (with a 2.5 mm ² conductor cross-section)
Nominal voltage	450 V (Only use secured in place.)

Dimensions

Width	16.2 mm
Height	13.4 mm
Depth	16.2 mm
Drill hole spacing	8 mm
Pitch	8 mm

Material specifications

Color	transparent
Flammability rating according to UL 94	V2
Insulating material	PA

EC 2,5 P TR - Europe connectors



3240167

<https://www.phoenixcontact.com/us/products/3240167>

Mechanical properties

Mechanical data

Open side panel

No

Technical data

Drill hole spacing

8 mm

Mounting

Mounting type

direct screw connection

EC 2,5 P TR - Europe connectors

3240167

<https://www.phoenixcontact.com/us/products/3240167>



Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

EC 2,5 P TR - Europe connectors



3240167

<https://www.phoenixcontact.com/us/products/3240167>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	752ad24f-4ef2-426b-8b6f-315c2b38fa3b

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com