

EC 25 TR - Europe connectors



3240185

<https://www.phoenixcontact.com/us/products/3240185>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Polyamide Europe terminal strip, transparent, for connecting solid conductors and stranded conductors with ferrules with a cross section of 10 to 25 mm²

Commercial data

Item number	3240185
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE73
Product key	BE7321
GTIN	4046356457897
Weight per piece (including packing)	117.44 g
Weight per piece (excluding packing)	117.44 g
Customs tariff number	85369010
Country of origin	AT

3240185

<https://www.phoenixcontact.com/us/products/3240185>

Technical data

Product properties

Product type	Europe connector
Number of positions	12
Pitch	16 mm
Number of connections	24
Number of rows	1

Electrical properties

Maximum power dissipation for nominal condition	3.26 W
---	--------

Connection data

Nominal cross section	25 mm ²
Connection method	Screw connection
Screw thread	M5
Tightening torque	2 ... 3 Nm
Stripping length	9 mm
Conductor cross-section rigid	10 mm ² ... 25 mm ²
Cross section AWG	8 ... 4 (converted acc. to IEC)
Conductor cross-section flexible	10 mm ² ... 25 mm ²
Conductor cross-section, flexible [AWG]	8 ... 4 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	4 mm ² ... 16 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	4 mm ² ... 10 mm ²
2 conductors with same cross section, rigid	4 mm ² ... 6 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	2.5 mm ² ... 4 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	1.5 mm ² ... 6 mm ²
Nominal cross section	25 mm ²
Nominal current	101 A (with 25 mm ² conductor cross-section)
Maximum load current	101 A (with 25 mm ² conductor cross-section)
Nominal voltage	750 V

Dimensions

Width	30 mm
Height	28 mm
Depth	30 mm
Drill hole spacing	16 mm
Pitch	16 mm

Material specifications

Color	transparent
Flammability rating according to UL 94	V2

EC 25 TR - Europe connectors



3240185

<https://www.phoenixcontact.com/us/products/3240185>

Insulating material	PA
---------------------	----

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Technical data

Drill hole spacing	16 mm
--------------------	-------

Mounting

Mounting type	direct screw connection
---------------	-------------------------

EC 25 TR - Europe connectors



3240185

<https://www.phoenixcontact.com/us/products/3240185>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

3240185

<https://www.phoenixcontact.com/us/products/3240185>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	35b0de99-94f9-4167-9418-885122c875c6

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com