WT-STEEL SH 4,6X520 - Cable tie

3240824

https://www.phoenixcontact.com/us/products/3240824

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders, made from rust-free stainless steel (AISI 316), suitable for the harshest of ambient conditions (for example, salt water), with ball lock, for quick and secure bundling and fastening

Commercial data

Item number	3240824
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BE07
Product key	BE7132
GTIN	4046356705721
Weight per piece (including packing)	5.54 g
Weight per piece (excluding packing)	5.54 g
Customs tariff number	73269098
Country of origin	GB

Technical data

Product properties

Product type	Cable tie
Tensile strength GRP	890 N

Dimensions

Width	4.6 mm
Length	520 mm
Max. material thickness	0.25 mm

Material specifications

RoHS compliant	yes
Color	silver-colored
Material	Stainless steel 1.4401/AISI 316
Components	free from silicone and halogen

Cable/line

External cable diameter	≤ 152.00 mm
Tensile strength	890 N

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-80 °C ... 538 °C
Ambient temperature (assembly)	-80 °C ... 538 °C
Resistance to UV radiation	yes
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

Mounting

Mounting type	Cannot be removed

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/3240824

cULus Listed
Approval ID: E328576

DNV
Approval ID: TAE000057Y

Classifications

ECLASS

ECLASS-13.0	27140702
ECLASS-15.0	27140702

ETIM

ETIM 10.0	EC000046

UNSPSC

UNSPSC 21.0	39121700

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com