

WP-STEEL ZC 14 - Protective hose



3240865

<https://www.phoenixcontact.com/us/products/3240865>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hose, material: Steel, galvanized, degree of protection: IP40, color: silver-colored, inside diameter: 11 mm, Total length: 10 m

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3240865 |
| Packing unit | 1 m |
| Minimum order quantity | 10 m |
| Sales key | BF68 |
| Product key | AF7DSA |
| GTIN | 4046356737173 |
| Weight per piece (including packing) | 999.9 g |
| Weight per piece (excluding packing) | 999.9 g |
| Customs tariff number | 83071000 |
| Country of origin | DE |

WP-STEEL ZC 14 - Protective hose



3240865

<https://www.phoenixcontact.com/us/products/3240865>

Technical data

Notes

| | |
|--------------------|--|
| Notes on operation | Protective hose length is measured stretched out; length tolerance $\pm 5\%$ |
|--------------------|--|

Product properties

| | |
|----------------------|-----------------|
| Product type | Protective hose |
| Tensile strength GRP | 500 N |

Dimensions

Internal dimensions

| | |
|-------------------|-------|
| Internal diameter | 11 mm |
|-------------------|-------|

Material specifications

| | |
|------------|-------------------|
| Material | Steel, galvanized |
| Components | halogen-free |

Cable/line

| | |
|-------------------------|-------|
| Bending radius, dynamic | 70 mm |
| Bending radius, static | 28 mm |
| Tensile strength | 500 N |
| Halogen-free | yes |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP40 |
| Ambient temperature (operation) | -50 °C ... 250 °C |


WP-STEEL ZC 14 - Protective hose



3240865

<https://www.phoenixcontact.com/us/products/3240865>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240865>



VDE approval of drawings

WP-STEEL ZC 14 - Protective hose



3240865

<https://www.phoenixcontact.com/us/products/3240865>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27430301 |
| ECLASS-15.0 | 27430301 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001179 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 40141700 |
|-------------|----------|

WP-STEEL ZC 14 - Protective hose



3240865

<https://www.phoenixcontact.com/us/products/3240865>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com