

WP-BASE HF 22 - Hose clamp

3240970

<https://www.phoenixcontact.com/us/products/3240970>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Hose clamp, material: Steel, galvanized, color: black/silver



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3240970 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BF68 |
| Product key | AF7DSA |
| GTIN | 4046356710886 |
| Weight per piece (including packing) | 9.9 g |
| Weight per piece (excluding packing) | 14.3 g |
| Customs tariff number | 39174000 |
| Country of origin | DE |

WP-BASE HF 22 - Hose clamp



3240970

<https://www.phoenixcontact.com/us/products/3240970>

Technical data

Product properties

| | |
|--------------|-------------------|
| Product type | Mounting material |
|--------------|-------------------|

Dimensions

| | |
|---------------|--------|
| Diameter | 22 mm |
| Hole diameter | 5.5 mm |

Material specifications

| | |
|------------|-------------------|
| Material | Steel, galvanized |
| Components | halogen-free |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

Mounting

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

WP-BASE HF 22 - Hose clamp

3240970

<https://www.phoenixcontact.com/us/products/3240970>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-15.0 | 27430315 |
| ECLASS-13.0 | 27430315 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31162900 |
|-------------|----------|

WP-BASE HF 22 - Hose clamp



3240970

<https://www.phoenixcontact.com/us/products/3240970>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.296 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com