

WP-GT BRASS PG36 - Protective hose screw connection

3241029

<https://www.phoenixcontact.com/us/products/3241029>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable gland made from brass with Pg thread, rotatable, IP40 protection



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3241029 |
| Packing unit | 2 pc |
| Minimum order quantity | 2 pc |
| Sales key | BF68 |
| Product key | AF7DSA |
| GTIN | 4046356711654 |
| Weight per piece (including packing) | 167.5 g |
| Weight per piece (excluding packing) | 167.5 g |
| Customs tariff number | 74122000 |
| Country of origin | DE |

WP-GT BRASS PG36 - Protective hose screw connection



3241029

<https://www.phoenixcontact.com/us/products/3241029>

Technical data

Product properties

| | |
|------------------------------|----------------------------------|
| Product type | Protective hose screw connection |
| Type of the screw connection | Conduit adapter |
| Cable outlet | straight |
| Thread type | Pg |

Dimensions

| | |
|--------------------------|-------|
| Width | 58 mm |
| Height | 40 mm |
| Length | 40 mm |
| Wrench size | 55 mm |
| Wrench size for mounting | 55 mm |

External dimensions

| | |
|------------------|-------|
| Outside diameter | 45 mm |
|------------------|-------|

Internal dimensions

| | |
|-------------------|---------|
| Internal diameter | 36.5 mm |
|-------------------|---------|

Material specifications

| | |
|------------|----------------------|
| Color | brass color |
| Material | Brass, nickel-plated |
| Components | halogen-free |

Mechanical properties

Mechanical data

| | |
|------------------------------|-----------------|
| Type of the screw connection | Conduit adapter |
|------------------------------|-----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP40 |
| Ambient temperature (operation) | -40 °C ... 250 °C |

WP-GT BRASS PG36 - Protective hose screw connection



3241029

<https://www.phoenixcontact.com/us/products/3241029>

Classifications

ECLASS

ECLASS-13.0

27430310

ETIM

ETIM 9.0

EC001180

UNSPSC

UNSPSC 21.0

40141700

WP-GT BRASS PG36 - Protective hose screw connection



3241029

<https://www.phoenixcontact.com/us/products/3241029>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | aa098d2f-01af-44db-8be0-ba15a3531e38 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com