WP-CN PA M40 - Counter nut

3241137

https://www.phoenixcontact.com/us/products/3241137

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads M40, color: gray



Your advantages

- The polyamide counter nuts are used to lock protective hose screw connections in the case of bore holes without a thread.

Commercial data

Item number	3241137
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356785433
Weight per piece (including packing)	6.532 g
Weight per piece (excluding packing)	3.272 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Product type	Flat nut
Thread type	M40

Dimensions

Height	7 mm
Thread type connection side	M40

Material specifications

Material	Polyamide fiberglass reinforced

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C

Classifications

ECLASS

ECLASS-13.0	27140807
ECLASS-15.0	27140807

ETIM

ETIM 10.0	EC003608

UNSPSC

UNSPSC 21.0	31161700

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.328 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com