WP-CN BRASS PG29 - Counter nut

3241157

https://www.phoenixcontact.com/us/products/3241157

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads Pg29, color: silver-colored



Your advantages

- The brass counter nuts are used to lock protective hose screw connections in the case of bore holes without a thread.

Commercial data

Item number	3241157
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356785631
Weight per piece (including packing)	12.31 g
Weight per piece (excluding packing)	12.31 g
Customs tariff number	74153300
Country of origin	DE

Technical data

Product properties

Product type	Flat nut
Thread type	Pg29

Dimensions

Height	4 mm
Thread type connection side	Pg29

Material specifications

Material	Brass, nickel-plated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 200 °C

Classifications

ECLASS

ECLASS-13.0	27140807
ECLASS-15.0	27140807

ETIM

ETIM 10.0	EC003608

UNSPSC

UNSPSC 21.0	31161700

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	cd912c84-624f-4ccc-a22d-949c5dd2ea28

EF3.1 Climate Change

CO2e kg	0.309 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com