# A 50 -40 - Ferrule

3241240

https://www.phoenixcontact.com/us/products/3241240

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Length contact range: 40 mm, sleeve length: 40 mm, color: silver-colored

## Your advantages

- The insulation reliability of close connections is increased and the splicing of wires is prevented

## Commercial data

| | |
|---|---|
| Item number | 3241240 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BH34 |
| Product key | BH3412 |
| GTIN | 4046356908139 |
| Weight per piece (including packing) | 3.6 g |
| Weight per piece (excluding packing) | 3.63 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

## Technical data

### Notes

| | |
|---|---|
| General | These ferrules are not included in DIN 46228-1: 1992-08 |

### Product properties


| | |
|---|---|
| Product type | Cable end sleeve |
| Conductor category | stranded conductors, class 2, 5, 6 / B, C, K, M |
| Product property | Made from soft tin-plated electrolytic copper |
| | Correspond to the requirements of DIN 46228-4 and UL 486F in terms of size |
| | Long/short-term temperature: +105°C/+120°C |

### Connection data

Conductor connection

| | |
|---|---|
| Conductor cross-section flexible max. | 50 mm² |
| Conductor cross-section AWG max. | 1/0 |
| Stripping length | 40 mm |

### Dimensions

| | |
|---|---|
| Dimensional drawing |  |
| Sleeve length | 40 mm |
| Length contact range | 40 mm |
| Maximum stripping length | 40 mm |
| Ferrule diameter | 10.3 mm |
| Sleeve wall thickness | 0.3 mm |
| Inner dimensions of the insulating collar | 13 mm |

### Material specifications

| | |
|---|---|
| Color | silver-colored |
| Material | CU-DHP |
| Coating | galvanically tin-plated |
| Surface characteristics | Tin-plated |

### Mechanical properties

Technical data

| | |
|---|---|
| Sleeve length | 40 mm |


### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Permanent temperature | 105 °C |
| Short-term temperature | 120 °C |

## Drawings

Dimensional drawing




Sleeve length (b), insulating collar inner dimension (d), sleeve diameter (k), sleeve wall thickness (j)

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27400201 |
| ECLASS-15.0 | 27400201 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000005 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 27121700 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 0.132 kg CO2e |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com