

HC-RBO 8-FE - Covering hood

3247968

<https://www.phoenixcontact.com/us/products/3247968>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Covering hood, depth: 46.7 mm, width: 28.8 mm, height: 85.6 mm, color: black/yellow



Commercial data

Item number	3247968
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z1X
GTIN	4046356719247
Weight per piece (including packing)	12.08 g
Weight per piece (excluding packing)	11.77 g
Customs tariff number	85389099
Country of origin	IN

HC-RBO 8-FE - Covering hood



3247968

<https://www.phoenixcontact.com/us/products/3247968>

Technical data

Product properties

Product type	Cover profile
--------------	---------------

Dimensions

Width	28.8 mm
Height	85.6 mm
Depth	46.7 mm

Material specifications

Color	multicolored (RAL -)
	black (RAL 9005)
	yellow (RAL 1018)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

HC-RBO 8-FE - Covering hood

3247968

<https://www.phoenixcontact.com/us/products/3247968>



Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27250190

ETIM

ETIM 10.0	EC002848
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-RBO 8-FE - Covering hood



3247968

<https://www.phoenixcontact.com/us/products/3247968>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com