

HC-RBO 16 BU - Covering hood

3247998

<https://www.phoenixcontact.com/us/products/3247998>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Covering hood, depth: 33 mm, width: 54.8 mm, height: 164 mm, color: blue



Commercial data

Item number	3247998
Packing unit	6 pc
Minimum order quantity	6 pc
Product key	BE1Z1X
GTIN	4046356724470
Weight per piece (including packing)	49.691 g
Weight per piece (excluding packing)	49.691 g
Country of origin	IN

HC-RBO 16 BU - Covering hood



3247998

<https://www.phoenixcontact.com/us/products/3247998>

Technical data

Product properties

Product type	Cover profile
--------------	---------------

Dimensions

Width	54.8 mm
Height	164 mm
Depth	33 mm

Material specifications

Color	blue (RAL 5015)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

HC-RBO 16 BU - Covering hood



3247998

<https://www.phoenixcontact.com/us/products/3247998>

Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27250190

ETIM

ETIM 10.0	EC002848
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-RBO 16 BU - Covering hood



3247998

<https://www.phoenixcontact.com/us/products/3247998>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com