

EB 2-25/PT - Insertion bridge



3260157

<https://www.phoenixcontact.com/us/products/3260157>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insertion bridge, pitch: 25 mm, number of positions: 2, nominal current: 150 A, length: 73 mm, color: red



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3260157 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE29 |
| Product key | BE2Z2X |
| GTIN | 4046356779111 |
| Weight per piece (including packing) | 50.6 g |
| Weight per piece (excluding packing) | 50.6 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

EB 2-25/PT - Insertion bridge



3260157

<https://www.phoenixcontact.com/us/products/3260157>

Technical data

Product properties

| | |
|---------------------|------------------|
| Product type | Insertion bridge |
| Number of positions | 2 |
| Pitch | 25 mm |

Electrical properties

| | |
|----------------------|-------|
| Maximum load current | 150 A |
|----------------------|-------|

Connection data

| | |
|----------------------|-------|
| Maximum load current | 150 A |
|----------------------|-------|

Dimensions

| | |
|--------|---------|
| Width | 47.8 mm |
| Height | 73.3 mm |
| Depth | 28.6 mm |
| Length | 73.3 mm |
| Pitch | 25 mm |

Material specifications

| | |
|--|----------------|
| Color | red (RAL 3001) |
| Material | Metal |
| Flammability rating according to UL 94 | V0 |
| Coating | tin-plated |
| Insulating material | PA |

Mounting

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

EB 2-25/PT - Insertion bridge



3260157

<https://www.phoenixcontact.com/us/products/3260157>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250303 |
| ECLASS-15.0 | 27250303 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000489 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

EB 2-25/PT - Insertion bridge



3260157

<https://www.phoenixcontact.com/us/products/3260157>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.906 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com