

UMK-SE 11,25-3 - Lateral element



5030266

<https://www.phoenixcontact.com/us/products/5030266>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Side element, 11.25 mm wide, without marker groove

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 5030266 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Note | Made to order (non-returnable) |
| Sales key | AC13 |
| Product key | ACHDCA |
| GTIN | 4017918287238 |
| Weight per piece (including packing) | 5.38 g |
| Weight per piece (excluding packing) | 5.38 g |
| Customs tariff number | 85389099 |
| Country of origin | PL |

UMK-SE 11,25-3 - Lateral element



5030266

<https://www.phoenixcontact.com/us/products/5030266>

Technical data

Product properties

| | |
|------------------------------|-------------------------------|
| Product type | Panel mounting base side part |
| Housing type | Press-drawn section housings |
| Housing series | UMK |
| Product family | UMK SE |
| Ventilation openings present | no |

Dimensions

| | |
|--------|----------|
| Length | 11.25 mm |
|--------|----------|

External dimensions

| | |
|--------------------------|-------|
| Profile width (external) | 77 mm |
|--------------------------|-------|

Internal dimensions

| | |
|--------------------------|---------|
| Profile width (internal) | 72.2 mm |
|--------------------------|---------|

Material specifications

| | |
|----------------------------------------|------------------|
| Color (Side element) | green (RAL 6021) |
| Material Lateral element | PA |
| Flammability rating according to UL 94 | V2 |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|----------------------------------------------------|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
|---------------------------------|----------------------------------------------------|

UMK-SE 11,25-3 - Lateral element



5030266

<https://www.phoenixcontact.com/us/products/5030266>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/5030266>



UL Recognized

Approval ID: E240868

UMK-SE 11,25-3 - Lateral element



5030266

<https://www.phoenixcontact.com/us/products/5030266>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190602 |
| ECLASS-15.0 | 27190602 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UMK-SE 11,25-3 - Lateral element



5030266

<https://www.phoenixcontact.com/us/products/5030266>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

China RoHS

| | |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 0.04 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com