

THERMOMARK X1.2 - Thermal transfer printer



5146231

<https://www.phoenixcontact.com/us/products/5146231>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal transfer printer, weight: 10 kg, length: 0.446 m, width: 242 mm, height: 274 mm, color: gray

Commercial data

Item number	5146231
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BG01
Product key	BG1221
GTIN	4046356484817
Weight per piece (including packing)	9,750 g
Weight per piece (excluding packing)	9,750 g
Customs tariff number	84433210
Country of origin	DE

THERMOMARK X1.2 - Thermal transfer printer



5146231

<https://www.phoenixcontact.com/us/products/5146231>

Technical data

Product properties

Product type	Marking system
--------------	----------------

Marking

Identification technology	Thermotransfer
---------------------------	----------------

Device properties

Print width	105 mm
Operating system	MS Windows Vista, MS Windows 7 (32/64-bit), MS Windows 8 (32/64-bit), MS Windows 8.1 (32/64-bit), MS Windows 10 (32/64-bit), Server 2008, Server 2008 R2, Server 2012, Server 2012 R2

Electrical properties

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	---

Dimensions

Width	242 mm
Height	274 mm
Length	446 mm

Material specifications

Color	gray
-------	------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	10 °C ... 35 °C
---------------------------------	-----------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com