

THERMOMARK S1.1 - Thermal transfer printer



5146257

<https://www.phoenixcontact.com/us/products/5146257>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal transfer printer, weight: 2 kg, length: 0.25 m, width: 230 mm, height: 170 mm, color: gray

Commercial data

Item number	5146257
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	BG1221
GTIN	4046356485692
Weight per piece (including packing)	4.9 kg
Weight per piece (excluding packing)	4.9 kg
Customs tariff number	84433210
Country of origin	TW

THERMOMARK S1.1 - Thermal transfer printer



5146257

<https://www.phoenixcontact.com/us/products/5146257>

Technical data

Product properties

Product type	Marking system
--------------	----------------

Marking

Identification technology	Thermotransfer
---------------------------	----------------

Device properties

Print width	100 mm
Operating system	MS Windows XP SP3, MS Windows Vista Business, MS Windows 7 Professional (32/64-bit), MS Windows 8 (32/64-bit)

Electrical properties

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	---

Dimensions

Width	230 mm
Height	170 mm
Length	250 mm

Material specifications

Color	gray
-------	------

THERMOMARK S1.1 - Thermal transfer printer



5146257

<https://www.phoenixcontact.com/us/products/5146257>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com