

THERMOMARK ROLL - Thermal transfer printer



5146477

<https://www.phoenixcontact.com/us/products/5146477>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal transfer printer, 300 dpi, incl. European power cable, US power cable, and USB cable. DVD with CLIP PROJECT advanced planning and marking software, user manuals in various languages, Windows® printer driver, and firmware. German/English user manual in DIN A5 format, EML (20x8)R roll of labels, white, with 1000 labels, and ink ribbon: 50 m

Product description

The THERMOMARK ROLL processes material off the roll and continuous media. You can easily create high-quality printed labels and markers.

Commercial data

Item number	5146477
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BG01
Product key	BG1221
GTIN	4046356528566
Weight per piece (including packing)	5,875.5 g
Weight per piece (excluding packing)	5,875.5 g
Customs tariff number	84433210
Country of origin	DE

5146477

<https://www.phoenixcontact.com/us/products/5146477>

Technical data

Product properties

Product type	Marking system
--------------	----------------

Marking

Identification technology	Thermotransfer
---------------------------	----------------

Device properties

Print width	104 mm
Print resolution	300 dpi
Operating system	MS Windows Vista, MS Windows 7 (32/64-bit), MS Windows 8 (32/64-bit), MS Windows 8.1 (32/64-bit), MS Windows 10 (32/64-bit), Server 2008, Server 2008 R2, Server 2012, Server 2012 R2

Electrical properties

Power consumption	45 W
-------------------	------

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	---

Dimensions

Width	240 mm
Height	189 mm
Length	320 mm

Material specifications

Color	gray
-------	------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 40 °C
Permissible humidity (operation)	10 % ... 85 %

THERMOMARK ROLL - Thermal transfer printer



5146477

<https://www.phoenixcontact.com/us/products/5146477>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/5146477>



IECEE CB Scheme

Approval ID: DK-5163-A1-UL



UL Listed

Approval ID: E140403



cUL Listed

Approval ID: E140403



KC

Approval ID: KCCREIPCK-FL5146477

5146477

<https://www.phoenixcontact.com/us/products/5146477>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com