

# BLUEMARK MAG AI-WM - Magazine



5146567

<https://www.phoenixcontact.com/us/products/5146567>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Magazine for BLUEMARK printer, for accommodating 0.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup> ferrules with insulating collar that can be labeled



## Commercial data

Item number	5146567
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG03
Product key	BG121Z
GTIN	4046356547567
Weight per piece (including packing)	47 g
Weight per piece (excluding packing)	47 g
Customs tariff number	90179000
Country of origin	DE

5146567

<https://www.phoenixcontact.com/us/products/5146567>

## Technical data

### Product properties

Product type	Magazine
--------------	----------

### Dimensions

Width	76 mm
Height	120 mm
Depth	4 mm

### Material specifications

Color	gray
-------	------

5146567

<https://www.phoenixcontact.com/us/products/5146567>

## Classifications

### ECLASS

ECLASS-13.0	19140615
ECLASS-15.0	19140615

### ETIM

ETIM 10.0	EC001675
-----------	----------

### UNSPSC

UNSPSC 21.0	43211600
-------------	----------

5146567

<https://www.phoenixcontact.com/us/products/5146567>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)