# THERMOMARK ROLL SET RU RU - Thermal transfer printer set

5147222

https://www.phoenixcontact.com/us/products/5147222

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

**Printing set,** consisting of: 1 x THERMOMARK ROLL, Order No. 5146477, 1 x MARKING NOTEBOOK (DELL; without internal CD/DVD drive), CLIP-PROJECT PROFESSIONAL

## Commercial data

| | |
|---|---|
| Item number | 5147222 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | BG1222 |
| GTIN | 4046356699853 |
| Weight per piece (including packing) | 999 g |
| Weight per piece (excluding packing) | 999 g |
| Country of origin | DE |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Marking system |

Marking

| | |
|---|---|
| Identification technology | Thermotransfer |

Device properties

| | |
|---|---|
| Print width | 104 mm |
| Print resolution | 300 dpi |
| Operating system | MS Windows 7, MS Windows 8.1, MS Windows 10 |

### System properties

| | |
|---|---|
| Operating system | MS Windows 7, MS Windows 8.1, MS Windows 10 |

### Electrical properties

Supply

| | |
|---|---|
| Supply voltage range | 100 V AC ... 240 V AC (50 Hz ... 60 Hz) |

### Dimensions

| | |
|---|---|
| Width | 380 mm |
| Height | 189 mm |
| Length | 320 mm |

### Material specifications

| | |
|---|---|
| Color | gray |

### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | 5 °C ... 35 °C |
| Permissible humidity (operation) | 10 % ... 80 % |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com