THERMOMARK ROLL SET RU RU - Thermal transfer printer set

5147222

https://www.phoenixcontact.com/us/products/5147222

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Printing set, consisting of: 1 x THERMOMARK ROLL, Order No. 5146477, 1 x MARKING NOTEBOOK (DELL; without internal CD/DVD drive), CLIP-PROJECT PROFESSIONAL

Commercial data

Item number	5147222
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BG1222
GTIN	4046356699853
Weight per piece (including packing)	999 g
Weight per piece (excluding packing)	999 g
Country of origin	DE

Technical data

Product properties

Product type	Marking system

Marking

Identification technology	Thermotransfer

Device properties

Print width	104 mm
Print resolution	300 dpi
Operating system	MS Windows 7, MS Windows 8.1, MS Windows 10

System properties

Operating system	MS Windows 7, MS Windows 8.1, MS Windows 10

Electrical properties

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)

Dimensions

Width	380 mm
Height	189 mm
Length	320 mm

Material specifications

Color	gray

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 35 °C
Permissible humidity (operation)	10 % ... 80 %

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com