

# UMK 33-REL NI/4X21-ST - Relay base



5521830

<https://www.phoenixcontact.com/us/products/5521830>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE base module for 4PDT relays

## Your advantages

- Pluggable relay
- Safe isolation between coil and contact side
- 5 amp 4 PDT rating
- Arc barriers between adjacent poles

## Commercial data

Item number	5521830
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK6165
GTIN	4046356683821
Weight per piece (including packing)	33.33 g
Weight per piece (excluding packing)	33.33 g
Customs tariff number	85364190
Country of origin	US

5521830

<https://www.phoenixcontact.com/us/products/5521830>

## Technical data

### Product properties

Product type	Relay socket
Application	Universal
Operating mode	100% operating factor

### Electrical properties

Nominal voltage $U_N$	250 V AC/DC
	250 V AC/DC
Nominal current $I_N$	5 A

### Connection data

#### Input side

Connection method	Screw connection
Stripping length	6 mm
Screw thread	M3
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	30 ... 14

#### Output side

Connection method	Screw connection
Stripping length	6 mm
Screw thread	M3
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	30 ... 14

### Dimensions

Width	33.75 mm
Height	77 mm
Depth Retaining bracket	71.4 mm (with relay)

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

### Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

# UMK 33-REL NI/4X21-ST - Relay base



5521830

<https://www.phoenixcontact.com/us/products/5521830>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)