

# UMK 22 REL 24/21-21-ST (BASE) - Relay base




5529191

<https://www.phoenixcontact.com/us/products/5529191>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE base module for G2R relay, 2PDT



## Your advantages

- Relay base family that can be fitted with 2 changeover contact relay
- Safe isolation between coil and contact side
- For use with Omron G2R-2-S relays
- DIN rail mounting

## Commercial data

Item number	5529191
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK61Y2
GTIN	4046356684163
Weight per piece (including packing)	33.33 g
Weight per piece (excluding packing)	33.33 g
Customs tariff number	85364190
Country of origin	US

# UMK 22 REL 24/21-21-ST (BASE) - Relay base



5529191

<https://www.phoenixcontact.com/us/products/5529191>

## Technical data

### Product properties

Product type	Relay socket
Application	Universal
Operating mode	100% operating factor

### Electrical properties

Nominal voltage $U_N$	250 V AC/DC
Nominal current $I_N$	5 A

### Connection data

#### Input side

Connection method	Screw connection
Stripping length	6 mm
Screw thread	M3
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	30 ... 14

#### Output side

Connection method	Screw connection
Stripping length	6 mm
Screw thread	M3
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	30 ... 14

### Dimensions

Width	22.5 mm
Height	77 mm
Depth Retaining bracket	50 mm (with retaining bracket)

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

### Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

5529191

<https://www.phoenixcontact.com/us/products/5529191>

## Classifications

### ECLASS

ECLASS-13.0	27371603
ECLASS-15.0	27371603

### ETIM

ETIM 10.0	EC001456
-----------	----------

5529191

<https://www.phoenixcontact.com/us/products/5529191>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)