

UMK 22-REL 24/21-21 - Relay module




5542754

<https://www.phoenixcontact.com/us/products/5542754>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE relay module, fixed, 2PDT



UMK 22 REL 24 VAC/21-21 shown

Your advantages

- Safe isolation between coil and contact side

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 5542754 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C460 |
| Product key | DK61Y2 |
| GTIN | 4046356687096 |
| Weight per piece (including packing) | 33.33 g |
| Weight per piece (excluding packing) | 33.33 g |
| Customs tariff number | 85364190 |
| Country of origin | US |

UMK 22-REL 24/21-21 - Relay module



5542754

<https://www.phoenixcontact.com/us/products/5542754>

Technical data

Notes

Trade restriction

| | |
|---------|--|
| CE note | The products are offered exclusively for export outside the EU and the European Economic Area. |
|---------|--|

Product properties

| | |
|-------------------------|---------------------------|
| Product type | Relay Module |
| Application | Universal |
| Operating mode | 100% operating factor |
| Mechanical service life | 1x 10 ⁷ cycles |

Data management status

| | |
|------------------------------|------------|
| Date of last data management | 01.04.2026 |
|------------------------------|------------|

Electrical properties

| | |
|--------------------------------|--|
| Test voltage (Winding/contact) | 5 kV (50/60 Hz, 1 min., winding/contact) |
|--------------------------------|--|

Input data

Coil side

| | |
|--------------------------------|--------------------|
| Nominal input voltage U_N | 24 V DC |
| Typical input current at U_N | 32 mA |
| Typical response time | 15 ms |
| Typical release time | 5 ms |
| Protective circuit | Freewheeling diode |
| Operating voltage display | LED |

Output data

Switching

| | |
|-----------------------------|-----------------------|
| Contact switching type | 2 changeover contacts |
| Contact material | AgCdO |
| Maximum switching voltage | 250 V AC (30 V DC) |
| Minimum switching voltage | 5 V (at 10 mA) |
| Limiting continuous current | 5 A |
| Min. switching current | 10 mA (At 5 V) |

Connection data

Coil side

| | |
|----------------------------------|--|
| Connection method | Screw connection |
| Stripping length | 7 mm |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.14 mm ² ... 1.5 mm ² |

UMK 22-REL 24/21-21 - Relay module



5542754

<https://www.phoenixcontact.com/us/products/5542754>

| | |
|-----------------------------|-----------|
| Conductor cross-section AWG | 30 ... 14 |
|-----------------------------|-----------|

Contact side

| | |
|----------------------------------|--|
| Connection method | Screw connection |
| Stripping length | 7 mm |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.14 mm ² ... 1.5 mm ² |
| Conductor cross-section AWG | 30 ... 14 |

Dimensions

Item dimensions

| | |
|--------|---------|
| Width | 22.5 mm |
| Height | 77 mm |
| Depth | 50 mm |

Material specifications

| | |
|-------|------------------|
| Color | green (RAL 6021) |
|-------|------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 65 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

Mounting

| | |
|-------------------|---------------------------|
| Assembly note | in rows with zero spacing |
| Mounting position | any |

UMK 22-REL 24/21-21 - Relay module



5542754

<https://www.phoenixcontact.com/us/products/5542754>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27371601 |
| ECLASS-15.0 | 27371601 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001437 |
|----------|----------|

5542754

<https://www.phoenixcontact.com/us/products/5542754>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, Not qualified for the European market |
|---|---|

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com