

# FLKM 26-LONG LATCH - Termination board



5601703

<https://www.phoenixcontact.com/us/products/5601703>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with screw connection and flat-ribbon cable connector, for mounting on NS 32 or NS 35/7.5, with pin strip and short and long locking latches for socket strips, 26-pos.

The figure shows a 40-position version

## Commercial data

Item number	5601703
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C422
Product key	DK2BZZ
GTIN	4046356955959
Weight per piece (including packing)	99.99 g
Weight per piece (excluding packing)	99.99 g
Customs tariff number	85369010
Country of origin	DE

# FLKM 26-LONG LATCH - Termination board



5601703

<https://www.phoenixcontact.com/us/products/5601703>

## Technical data

### Product properties

Product type	Interface module
Number of positions	26

### Insulation characteristics

Overvoltage category	II
Pollution degree	2

### Electrical properties

Nominal voltage $U_N$	< 50 V AC
	60 V DC
Max. current carrying capacity per branch	1 A

### Connection data

#### Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

#### Controller level

Connection method	IDC/FLK pin strip
Number of positions	26
Pitch	2.54 mm

### Signaling

Status display present	no
------------------------	----

### Dimensions

#### Item dimensions

Width	78.8 mm
Height	77 mm
Depth	58.5 mm

### Material specifications

Color	green (RAL 6021)
Housing insulation material	Polyamide 6 green

### Environmental and real-life conditions

# FLKM 26-LONG LATCH - Termination board



5601703

<https://www.phoenixcontact.com/us/products/5601703>

## Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

## Mounting

Mounting position	any
-------------------	-----

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# FLKM 26-LONG LATCH - Termination board



5601703

<https://www.phoenixcontact.com/us/products/5601703>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)