

# RAD-ISM-900-ANT-LP-0-ASSY - Antenna



5606527

<https://www.phoenixcontact.com/us/products/5606527>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Low profile, omnidirectional antenna with CN-UB surge arrester, MCX (male) connector. Includes 17 ft. RG-58 cable with N (male) connector

## Commercial data

Item number	5606527
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DNC6A3
GTIN	4046356685764
Weight per piece (including packing)	33.33 g
Weight per piece (excluding packing)	33.33 g
Customs tariff number	85369010
Country of origin	US

# RAD-ISM-900-ANT-LP-0-ASSY - Antenna



5606527

<https://www.phoenixcontact.com/us/products/5606527>

## Technical data

### Product properties

Product type	Antenna
Gain	2.14 dBi

### Electrical properties

Frequency band	900 MHz
Frequency range	806 Hz ... 960 Hz

### Connection data

#### Connection technology

Connection method	N (male)
-------------------	----------

### Dimensions

Height	32 mm
Diameter	144 mm

### Cable/line

Cable length	17.00 in.
Cable type	RG-58U

# RAD-ISM-900-ANT-LP-0-ASSY - Antenna



5606527

<https://www.phoenixcontact.com/us/products/5606527>

## Environmental product compliance

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)