

AK-DST/UK - Marker carrier

1000708

<https://www.phoenixcontact.com/pc/products/1000708>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a combination of versions AK-DST-UK marker label and ESL 24 x 4 insert strips

Marker label, for marking groups of terminal blocks with the top marker groove at an angle of 45° e. g. UK terminal blocks, snaps into the marker groove, the marker carrier can be swung over by 120° and is labeled with EST 24 x 4 or ESL 24 x 4.

Commercial data

Item number	1000708
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	BG211A
GTIN	4017918010324
Weight per piece (including packing)	0.898 g
Weight per piece (excluding packing)	0.896 g
Customs tariff number	39269097
Country of origin	PL

1000708

<https://www.phoenixcontact.com/pc/products/1000708>

Technical data

Product properties

Product type	Marker carriers
--------------	-----------------

Dimensions

Width	6.00 mm
Height	39.80 mm
Depth	13.44 mm

Text field

Text field width	24 mm
Text field height	4 mm

Material specifications

Color	transparent
Material	PA/PC
Flammability rating according to UL 94	V2
Base element material	PA/polycarbonate (PC)
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Mounting

Mounting type	latching
---------------	----------

AK-DST/UK - Marker carrier



1000708

<https://www.phoenixcontact.com/pc/products/1000708>

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 10.0	EC002248
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

AK-DST/UK - Marker carrier



1000708

<https://www.phoenixcontact.com/pc/products/1000708>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.009 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com