

# ZB 5,08,QR:FORTL.ZAHLEN 21-30 - Zack marker strip



0809858:0021

<https://www.phoenixcontact.com/us/products/0809858:0021>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, 10-section, vertically labeled with the consecutive numbers: 21 ... 30, white, for terminal block width: 5.08 mm, mounting type: latching

## Commercial data

Item number	0809858:0021
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2122
GTIN	4017918781958
Weight per piece (including packing)	1.3 g
Weight per piece (excluding packing)	1.031 g
Customs tariff number	49119900
Country of origin	DE

## Technical data

### Product properties

Product type	Terminal marker
Pitch	5.08 mm

### Marking

Printing	21 ... 30
Slot type	high

### Mounting

Mounting type	latching
---------------	----------

### Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

### Dimensions

Width	5 mm
Pitch	5.08 mm

#### Text field

Text field width	4.98 mm
Text field height	10.50 mm

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

0809858:0021

<https://www.phoenixcontact.com/us/products/0809858:0021>

## Classifications

### ECLASS

ECLASS-13.0

27281101

### ETIM

ETIM 9.0

EC000761

### UNSPSC

UNSPSC 21.0

39131500

0809858:0021

<https://www.phoenixcontact.com/us/products/0809858:0021>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)