

# ES-BBC-MF4 - Panel-mount frame

1155607

<https://www.phoenixcontact.com/us/products/1155607>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Panel-mount frame, Range of articles: BBC, design: Panel-mount frame, color: black



The figure shows a 3-position version

## Commercial data

Item number	1155607
Packing unit	4 pc
Minimum order quantity	4 pc
Sales key	AB04
Product key	ABLDAC
GTIN	4063151157036
Weight per piece (including packing)	72.7 g
Weight per piece (excluding packing)	46.929 g
Customs tariff number	85389099
Country of origin	CN

# ES-BBC-MF4 - Panel-mount frame



1155607

<https://www.phoenixcontact.com/us/products/1155607>

## Technical data

### Product properties

Product type	Panel-mount frame
Product family	BBC
Type	Panel-mount frame
Number of slots	1

### Dimensions

Width	68 mm
Height	88 mm
Length	41 mm

### Material specifications

Color	black
Color of the housing part	black
Material Housing	PA-GF
Flammability rating according to UL 94	V0

### Cable/line

Halogen-free	yes
--------------	-----

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	1
-----------------------------	---

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-10 °C ... 50 °C
---------------------------------	------------------

# ES-BBC-MF4 - Panel-mount frame



1155607

<https://www.phoenixcontact.com/us/products/1155607>

## Classifications

### ECLASS

ECLASS-13.0	27440192
ECLASS-15.0	27440210

### ETIM

ETIM 10.0	EC002310
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# ES-BBC-MF4 - Panel-mount frame



1155607

<https://www.phoenixcontact.com/us/products/1155607>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)