STG 10-VBST 4 - Connector housing

0710976

https://www.phoenixcontact.com/gb/products/0710976

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector housing, depth: 45 mm, width: 61.3 mm, height: 14.7 mm, number of positions: 10, color: black

Commercial data

Item number	0710976
Packing unit	1,500 pc
Minimum order quantity	1,500 pc
Sales key	BE5Z3X
Product key	BE5Z3X
GTIN	4017918904289
Weight per piece (including packing)	9.9 g
Weight per piece (excluding packing)	9.9 g
Customs tariff number	85389099
Country of origin	DE

Technical data

Product properties

Product type	Mounting material
Number of positions	10

Dimensions

Width	61.3 mm
Height	14.7 mm
Depth	45 mm

Material specifications

Color	black (RAL 9005)
Material	PA
Flammability rating according to UL 94	V0
Static insulating material application in cold	-40 °C
Relative insulation material temperature index (Elec., UL 746 B)	120 °C

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

ETIM

ETIM 10.0	EC000437

UNSPSC

UNSPSC 21.0	31261500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.057 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk