

# HC-B 48-TFL-96/O1STM40G - Housing



1647310

<https://www.phoenixcontact.com/us/products/1647310>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON sleeve housing B48, for single locking latch, height 96 mm, with thread 1x M40, straight conductor exit

## Commercial data

Item number	1647310
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF55
Product key	AF7AAC
GTIN	4017918969462
Weight per piece (including packing)	686.2 g
Weight per piece (excluding packing)	588.2 g
Customs tariff number	85389099
Country of origin	DE

# HC-B 48-TFL-96/O1STM40G - Housing

1647310

<https://www.phoenixcontact.com/us/products/1647310>

## Technical data


### Notes

General	For contact inserts HC-B48, DD216, M
---------	--------------------------------------

### Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B48
No. of cable outlets	1
Type of the screw connection	1x M40
Shielded	no
Cable outlet	straight
Pg screw connection	none

### Dimensions

Dimensional drawing	
Width	89 mm
Height	96 mm
Length	131.5 mm

### Material specifications

Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray

### Mechanical properties

#### Mechanical data

Type of the screw connection	1x M40
Locking type	Pin

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

# HC-B 48-TFL-96/O1STM40G - Housing


1647310

<https://www.phoenixcontact.com/us/products/1647310>



## Drawings

Dimensional drawing



Dimensional drawing

# HC-B 48-TFL-96/O1STM40G - Housing



1647310

<https://www.phoenixcontact.com/us/products/1647310>

## Classifications

### ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

### UNSPSC

UNSPSC 21.0	31261501
-------------	----------

# HC-B 48-TFL-96/O1STM40G - Housing



1647310

<https://www.phoenixcontact.com/us/products/1647310>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)