


ZBF 7,5,QR:FORTL.ZAHLEN 21-30 - Zack marker strip

0809968:0021

<https://www.phoenixcontact.com/us/products/0809968:0021>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, 10-section, vertically labeled with the consecutive numbers: 21 ... 30, white, for terminal block width: 7.5 mm, mounting type: latching

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0809968:0021 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Product key | BG2122 |
| GTIN | 4017918785192 |
| Weight per piece (including packing) | 0.638 g |
| Weight per piece (excluding packing) | 0.438 g |
| Country of origin | DE |

ZBF 7,5,QR:FORTL.ZAHLEN 21-30 - Zack marker strip



0809968:0021

<https://www.phoenixcontact.com/us/products/0809968:0021>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Terminal marker |
| Pitch | 7.5 mm |

Marking

| | |
|-----------|-----------|
| Printing | 21 ... 30 |
| Slot type | flat |

Mounting

| | |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

Material specifications

| | |
|--|--------------------------------|
| Color | white (RAL 9010) |
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Dimensions

| | |
|-------|--------|
| Pitch | 7.5 mm |
|-------|--------|

Text field

| | |
|-------------------|---------|
| Text field width | 7.40 mm |
| Text field height | 5.20 mm |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

ZBF 7,5,QR:FORTL.ZAHLEN 21-30 - Zack marker strip



0809968:0021

<https://www.phoenixcontact.com/us/products/0809968:0021>

Classifications

ECLASS

ECLASS-13.0

27281101

ETIM

ETIM 9.0

EC000761

UNSPSC

UNSPSC 21.0

39131500

ZBF 7,5,QR:FORTL.ZAHLEN 21-30 - Zack marker strip



0809968:0021

<https://www.phoenixcontact.com/us/products/0809968:0021>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com