

ES-BBC-MF4 - Panel-mount frame

1155607

<https://www.phoenixcontact.com/us/products/1155607>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Panel-mount frame, Range of articles: BBC, design: Panel-mount frame, color: black



The figure shows a 3-position version

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1155607 |
| Packing unit | 4 pc |
| Minimum order quantity | 4 pc |
| Sales key | AB04 |
| Product key | ABLDAC |
| GTIN | 4063151157036 |
| Weight per piece (including packing) | 72.7 g |
| Weight per piece (excluding packing) | 46.929 g |
| Customs tariff number | 85389099 |
| Country of origin | CN |

ES-BBC-MF4 - Panel-mount frame



1155607

<https://www.phoenixcontact.com/us/products/1155607>

Technical data

Product properties

| | |
|-----------------|-------------------|
| Product type | Panel-mount frame |
| Product family | BBC |
| Type | Panel-mount frame |
| Number of slots | 1 |

Dimensions

| | |
|--------|-------|
| Width | 68 mm |
| Height | 88 mm |
| Length | 41 mm |

Material specifications

| | |
|--|-------|
| Color | black |
| Color of the housing part | black |
| Material Housing | PA-GF |
| Flammability rating according to UL 94 | V0 |

Cable/line

| | |
|--------------|-----|
| Halogen-free | yes |
|--------------|-----|

Mechanical properties

Mechanical data

| | |
|-----------------------------|---|
| Insertion/withdrawal cycles | 1 |
|-----------------------------|---|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -10 °C ... 50 °C |
|---------------------------------|------------------|

ES-BBC-MF4 - Panel-mount frame



1155607

<https://www.phoenixcontact.com/us/products/1155607>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440192 |
| ECLASS-15.0 | 27440210 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002310 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

ES-BBC-MF4 - Panel-mount frame



1155607

<https://www.phoenixcontact.com/us/products/1155607>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com