PTFIX 1,5-NS15A - DIN rail adapter

1049500

https://www.phoenixcontact.com/gb/products/1049500

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail adapter, for NS 15 for accommodating 1.5 mm^2 FIX blocks in horizontal direction, color: gray

Commercial data

Item number	1049500
Packing unit	30 pc
Minimum order quantity	30 pc
Sales key	BEAZ11
Product key	BEAZ11
GTIN	4055626662213
Weight per piece (including packing)	0.9 g
Weight per piece (excluding packing)	0.8 g
Customs tariff number	39269097
Country of origin	PL

Technical data

Product properties

Product type	Mounting material

Dimensions

Width	8 mm
Height	21.6 mm
Depth	10.85 mm

Material specifications

Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Classifications

ECLASS

ECLASS-13.0	27370419
ECLASS-15.0	27370419

ETIM

ETIM 10.0	EC001024

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.005 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk