

NS 35/ 7,5 PERF 250MM - DIN rail perforated



1207639

<https://www.phoenixcontact.com/gb/products/1207639>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail perforated, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

Commercial data

Item number	1207639
Packing unit	1 pc
Minimum order quantity	20 pc
Sales key	BH8422
Product key	BH8422
GTIN	4046356366489
Weight per piece (including packing)	80 g
Weight per piece (excluding packing)	80 g
Customs tariff number	72166190
Country of origin	DE

NS 35/ 7,5 PERF 250MM - DIN rail perforated



1207639


<https://www.phoenixcontact.com/gb/products/1207639>

Technical data

Product properties

Product type	DIN rail
--------------	----------

Dimensions

Dimensional drawing	
Width	35 mm
Hole width	15 mm
Height	7.5 mm
Hole height	6.2 mm
Length	250 mm
Drill hole spacing	25 mm

Material specifications

Color	silver
Material	Steel
Coating	galvanized, passivated with a thick layer

Standards and regulations

Connection in acc. with standard	IEC / EN
Tests	acc. to EN 60715


NS 35/ 7,5 PERF 250MM - DIN rail perforated

1207639

<https://www.phoenixcontact.com/gb/products/1207639>



Drawings



NS 35/ 7,5 PERF 250MM - DIN rail perforated



1207639

<https://www.phoenixcontact.com/gb/products/1207639>

Classifications

ECLASS

ECLASS-11.0	27400602
ECLASS-13.0	27400602
ECLASS-12.0	27400602

ETIM

ETIM 9.0	EC001285
----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

NS 35/ 7,5 PERF 250MM - DIN rail perforated



1207639

<https://www.phoenixcontact.com/gb/products/1207639>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk