# PTFIX 10/S-F - Flange

1082917

https://www.phoenixcontact.com/gb/products/1082917

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Flange, With screw fixing, for direct mounting of the 10 $mm^2$ FIX blocks, depth: 25.1 mm, width: 8.6 mm, height: 37 mm, color: gray

## Commercial data


| | |
|---|---|
| Item number | 1082917 |
| Packing unit | 20 pc |
| Minimum order quantity | 20 pc |
| Sales key | BEAZ11 |
| Product key | BEAZ11 |
| GTIN | 4055626817033 |
| Weight per piece (including packing) | 4.3 g |
| Weight per piece (excluding packing) | 4.3 g |
| Customs tariff number | 85389099 |
| Country of origin | PL |

# Technical data

## Product properties

| | |
|---|---|
| Product type | Mounting material |

## Dimensions

| | |
|---|---|
| Dimensional drawing |   |
| Width | 8.6 mm |
| Height | 37 mm |
| Depth | 25.1 mm |
| Hole diameter | 5.8 mm |

## Material specifications

| | |
|---|---|
| Color | gray (RAL 7042) |
| Material | PA |
| Flammability rating according to UL 94 | V0 |


## Environmental and real-life conditions

### Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

## Drawings

Dimensional drawing



## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/1082917

**EAC**
Approval ID: KZ7500651131219505

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27250302 |
| ECLASS-15.0 | 27250302 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC001041 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 0.026 kg CO2e |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk