

HSCP-CB 5U-7035 - Fastening clip

1056892

<https://www.phoenixcontact.com/gb/products/1056892>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



ME-IO Blockbelt, for 5 PCB connectors, color: light gray (similar RAL 7035)

Your advantages

- Enables the functional grouping of various connector plugs
- Simplifies service and maintenance work
- Fast mounting and removal of the clamps through a latch system

Commercial data

Item number	1056892
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	ACHECZ
Product key	ACHECZ
GTIN	4055626697864
Weight per piece (including packing)	0.548 g
Weight per piece (excluding packing)	0.46 g
Customs tariff number	85389099
Country of origin	PL

HSCP-CB 5U-7035 - Fastening clip



1056892

<https://www.phoenixcontact.com/gb/products/1056892>

Technical data

Product properties

Product type	Mounting material
Housing type	ME-IO Blockbelt
Housing series	ME-IO
Type	for 5 PCB connectors

Material specifications

Color (Housing)	light gray (RAL 7035)
Flammability rating according to UL 94	V0
Housing material	PA
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Snap in
---------------	---------

HSCP-CB 5U-7035 - Fastening clip



1056892

<https://www.phoenixcontact.com/gb/products/1056892>

Classifications

ECLASS

ECLASS-11.0	27182702
ECLASS-13.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HSCP-CB 5U-7035 - Fastening clip



1056892

<https://www.phoenixcontact.com/gb/products/1056892>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk