PHT22-MBL60-BU - Button

1108467

https://www.phoenixcontact.com/gb/products/1108467

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Mushroom button head, 22 mm, circular, button head diameter: 60 mm, blue, self-locking

Your advantages

- 22 mm mushroom button (60 mm) – extra large and eye-catching
- Self-retaining (latching) – ideal for safe switching functions
- Extra large actuating surface for fast, intuitive operation
- Robust industrial design for durable use
- Designed for modular combination with PHT22 contact and LED modules

Commercial data

Item number	1108467
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE6122
Product key	BE6122
GTIN	4063151014506
Weight per piece (including packing)	33.2 g
Weight per piece (excluding packing)	30.9 g
Country of origin	Information on the country of origin is provided with the delivery.

Technical data

Product properties

Product type	Actuator
Actuator type	Mushroom button
Function	Self-locking type
Extension of optional light source	No
with light source	No

Insulation characteristics

Degree of pollution	3

Dimensions

Width	60 mm
Height	60 mm
Depth Installation	47.9 mm
Diameter Mounting	22.3 mm

Material specifications

Color	blue
Front ring material	Metal
Front ring color	silver

Environmental and real-life conditions

Degree of protection (IP code)

Degree of protection	IP66

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 85 °C
Permissible humidity (operation)	≤ 95 % ((room temperature 25℃) no condensation)

Standards and regulations

Standards/specifications	IEC 60947-5-1
	GB 14048.5
	UL 60947-5-1

Mounting

Mounting type	Panel mount
Tightening torque	1 Nm ... 1.2 Nm

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/1108467

cULus Listed
Approval ID: E172140

CCC
Approval ID: 2024010305697836

Classifications

ECLASS

ECLASS-13.0	27371403
ECLASS-15.0	27371212

ETIM

ETIM 10.0	EC001038

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk