PHT22-FRD-BU - Button

1108691

https://www.phoenixcontact.com/gb/products/1108691

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Illuminated flat button, 22 mm, circular, blue, self-resetting

Your advantages

- 22 mm illuminated button – compact and modern
- Spring return (momentary action) – ideal for pulse/start functions
- With integrated lighting option for clear status display
- Designed for modular combination with PHT22 contact and LED modules
- Quick mounting in the control cabinet/control panel

Commercial data

Item number	1108691
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE6122
Product key	BE6122
GTIN	4063151015169
Weight per piece (including packing)	19.8 g
Weight per piece (excluding packing)	17.6 g
Customs tariff number	85389099
Country of origin	CN

Technical data

Product properties

Product type	Actuator
Actuator type	Flat button
Function	Automatic reset
Extension of optional light source	Yes
with light source	No

Dimensions

Width	29.6 mm
Height	29.6 mm

Material specifications

Color	blue
Front ring material	Metal
Front ring color	silver

Environmental and real-life conditions

Degree of protection (IP code)

Degree of protection	IP66

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 85 °C
Permissible humidity (operation)	≤ 95 % ((room temperature 25℃) no condensation)

Standards and regulations

Standards/specifications	IEC 60947-5-1
	GB 14048.5
	UL 60947-5-1

Mounting

Mounting type	Panel mount
Tightening torque	1 Nm ... 1.2 Nm

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/1108691

cULus Listed
Approval ID: E172140

CCC
Approval ID: 2024010305697836

TÜV Rheinland
Approval ID: R CN21G3UE 001

Classifications

ECLASS

ECLASS-15.0	27371210
ECLASS-13.0	27371210

ETIM

ETIM 10.0	EC000221

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk