

# WT-HT HF 4,5X200 BK - Cable tie



3240787

<https://www.phoenixcontact.com/us/products/3240787>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders for quick and secure bundling, heat stabilized to 125°C (also up to 145°C for brief periods)

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 3240787             |
| Packing unit                         | 1 pc                |
| Minimum order quantity               | 100 pc              |
| Sales key                            | BE07                |
| Product key                          | BE7131              |
| Catalog page                         | Page 617 (C-3-2019) |
| GTIN                                 | 4046356705059       |
| Weight per piece (including packing) | 1.325 g             |
| Weight per piece (excluding packing) | 1.389 g             |
| Customs tariff number                | 39269097            |
| Country of origin                    | IT                  |

# WT-HT HF 4,5X200 BK - Cable tie



3240787

<https://www.phoenixcontact.com/us/products/3240787>

## Technical data

### Product properties

|                      |                |
|----------------------|----------------|
| Product type         | Cable tie      |
| Type                 | Internal teeth |
| Tensile strength GRP | 220 N          |

### Dimensions

|        |        |
|--------|--------|
| Width  | 4.8 mm |
| Length | 200 mm |

### Material specifications

|  |                                |
|--|--------------------------------|
| Color                                  | black                          |
| Material                               | PA 6.6                         |
| Flammability rating according to UL 94 | V2                             |
| Components                             | free from silicone and halogen |

### Cable/line

|                         |                |
|-------------------------|----------------|
| External cable diameter | 3 mm ... 50 mm |
| Tensile strength        | 220 N          |

### Environmental and real-life conditions

#### Ambient conditions

|   |   |
|---|---|
| Optimum ambient temperature (storage/transport) | 23 °C 50 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat. |
| Ambient temperature (operation)                 | -40 °C ... 125 °C   |
| Ambient temperature (assembly)                  | -10 °C ... 60 °C  |
| Short-term temperature                          | 145 °C  |

### Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | Cannot be removed |
|---------------|-------------------|

# WT-HT HF 4,5X200 BK - Cable tie



3240787

<https://www.phoenixcontact.com/us/products/3240787>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27140702 |
| ECLASS-12.0 | 27140702 |
| ECLASS-13.0 | 27140702 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000046 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

# WT-HT HF 4,5X200 BK - Cable tie



3240787

<https://www.phoenixcontact.com/us/products/3240787>

## Environmental product compliance

|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

# WT-HT HF 4,5X200 BK - Cable tie

3240787

<https://www.phoenixcontact.com/us/products/3240787>



## Accessories

### UNIFOX-CT 4,8 - Cable tie tool

1212475

<https://www.phoenixcontact.com/us/products/1212475>



**Cable binder pliers**, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm

---

### UNIFOX-CT 4,8P - Cable tie tool

1212609

<https://www.phoenixcontact.com/us/products/1212609>



**Cable binder pliers**, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm

---

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)