

UM-BEFE 35-1 - Base element



2956660

<https://www.phoenixcontact.com/us/products/2956660>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Base element with snap-on foot, for mounting on NS 32 or NS 35/7.5 DIN rail, without ribs, L = 35 mm



Commercial data

Item number	2956660
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC13
Product key	ACHDDA
Catalog page	Page 763 (C-1-2013)
GTIN	4017918085889
Weight per piece (including packing)	20.34 g
Weight per piece (excluding packing)	20.15 g
Customs tariff number	85472000
Country of origin	PL

UM-BEFE 35-1 - Base element



2956660

<https://www.phoenixcontact.com/us/products/2956660>

Technical data

Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM BE
Type	Plug-in module base element
Ventilation openings present	no

Dimensions

Width	35 mm
Height	111 mm
Depth	27.7 mm

Material specifications

Color (Housing)	green (RAL 6021)
Housing material	PA
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

UM-BEFE 35-1 - Base element



2956660

<https://www.phoenixcontact.com/us/products/2956660>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2956660>



UL Recognized

Approval ID: E240868

UM-BEFE 35-1 - Base element



2956660

<https://www.phoenixcontact.com/us/products/2956660>

Classifications

ECLASS

ECLASS-11.0	27182701
ECLASS-13.0	27190601

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM-BEFE 35-1 - Base element



2956660

<https://www.phoenixcontact.com/us/products/2956660>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com