# SZS 1,2X8,0 VDE - Screwdriver

1205082

https://www.phoenixcontact.com/gb/products/1205082

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Screwdriver, slot-headed, VDE insulated, size: 1.2 x 8.0 x 175 mm, 2-component grip, with non-slip grip

## Your advantages

- For working on or in the vicinity of live parts up to 1000 V AC or 1500 V DC
- The tools feature ergonomic two-component safety handles
- Large contact surface of blades inside screw head
- Individually tested safety screwdrivers according to DIN EN 60900 (VDE 0682-201)

## Commercial data

| | |
|---|---|
| Item number | 1205082 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BH3144 |
| Product key | BH3144 |
| GTIN | 4017918019129 |
| Weight per piece (including packing) | 146 g |
| Weight per piece (excluding packing) | 146 g |
| Customs tariff number | 82054000 |
| Country of origin | CZ |

## Technical data

### Notes

Environmental Product Compliance

| | |
|---|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |

### Product properties

| | |
|---|---|
| Product type | Screwdriver tools |
| Type | Bladed |

### Connection data

| | |
|---|---|
| Output | Bladed |

### Dimensions

| | |
|---|---|
| Dimensional drawing |   |
| Width | 40 mm |
| Blade width | 8 mm |
| Blade height | 175 mm |
| Length | 287 mm |
| Wrench size | 0 mm |
| Wrench size for mounting | 0 mm |
| Blade thickness | 1.2 mm |

### Material specifications

| | |
|---|---|
| Material | alloyed tool steel |

### Standards and regulations

| | |
|---|---|
| Tests | DIN/ISO 2380-1 IEC 60900:2004 |

## Drawings

Dimensional drawing



## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/1205082

**EAC**
Approval ID: RU x-DE.xx08.B.02974

**VDE Zeichengenehmigung**
Approval ID: 086858

**EAC**
Approval ID: 7500525.13.12.00701

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 21040407 |
| ECLASS-15.0 | 21040407 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000158 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 27111700 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 1.943 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk